

HPP V4 Hybrid C-PFT housing straight



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 545 1320
Specification	HPP V4 Hybrid C-PFT housing straight
HARTING eCatalogue	https://b2b.harting.com/09455451320

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	for hybrid PCB jack, straight

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	4.28 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440202 Shell for industrial connectors