



部品構成  
PARTS CONSTRUCTION


部番 NO.	部品名 PART NAME	製品番号 ENG. NO.	個数 QUAN.	材質 MATERIAL
①	ハウジングアッセンブリ HOUSING ASS'Y	54180-0619	1	ハウジング: ガラス入り耐熱樹脂 UL 94V-0 色: 黒 HOUSING: G.F. HEAT RESISTANT PLASTIC UL94V-0 COLOR: BLACK ターミナル: りん青銅 t 0.3 TERMINAL: PHOSPHOR BRONZE t0.3 メッキ仕様 接点部: ニッケル下地金メッキ PLATING CONTACT AREA: GOLD OVER NICKEL 結線部: ニッケル下地錫メッキ WIRE TERMINATION AREA: TIN OVER NICKEL
②	カバーA COVER A	54181-0615	1	カバーA: ガラス入りポリカーボネイト樹脂 COVER A: POLYCARBONATE G.F. UL 94V-0 色: グレー UL94V-0 COLOR: GRAY スプリングラッチ: ステンレス鋼 t 0.4 SPRING LATCH: STAINLESS STEEL t0.4
③	カバーB COVER B	54182-0605	1	ガラス入りポリカーボネイト樹脂 UL 94V-0 色: グレー POLYCARBONATE G.F. UL94V-0 COLOR: GRAY
④	シェル カバー SHELL COVER	58299-0626	1	鋼 t 0.4 STEEL t0.4
⑤	シェル ボディ SHELL BODY	58300-0626	1	メッキ仕様: ニッケル下地、錫メッキ PLATING: NICKEL BASE, TIN PLATING
⑥	ケーブルクランプ CABLE CLAMP	58303-0000	1	ステンレス鋼 STAINLESS STEEL
⑦	十字穴付きナベ小ネジ CROSS RECESSED PAN HEAD MACHINE SCREW	59832-0009	2	黄銅(ネジサイズ: M2X4) BRASS (SCREW SIZE: M2X4)

## NOTES:


本製品は55100-0600の鉛フリー品である  
THIS PRODUCT IS LEAD FREE OF 55100-0600.




COVER A




COVER B




SHELL COVER




HOUSING ASS'Y



CABLE CLAMP



SCREW



SHELL BODY

GRAY COVER COLOR	TRAY & POLY BAG	55100-0680	55100-***0
	POLY BAG	55100-0670	
PACKAGE METHOD	PACKAGE METHOD	MATERIAL No.	MODEL No.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
DIMENSION UNITS	SCALE	CURRENT REV DESC:	
mm	NTS	EC NO: 627599	2.0 I/O CONN.PLUG SET
GENERAL TOLERANCES (UNLESS SPECIFIED)			
ANGULAR TOL $\pm$ ${}^\circ$		DRWN: KTAKEUCHI01	2019/10/02
4 PLACES	$\pm$	CHK'D: TKON	2019/11/19
3 PLACES	$\pm$	APPR: ASHIMOTSU	2019/11/19
2 PLACES	$\pm$	INITIAL REVISION:	
1 PLACE	$\pm$	DRWN: HKAWABATA	2004/05/21
0 PLACES	$\pm$	APPR: MSASAO	2004/05/21
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING
		SEE TABLE	A3-SIZE
		55100	SERIES
		1	1 OF 2



molex

部品構成  
PARTS CONSTRUCTION


部番 NO.	部品名 PART NAME	製品番号 ENG. NO.	個数 QUAN.	材質 MATERIAL
①	ハウジングアッセンブリ HOUSING ASS'Y	54180-0619	1	ハウジング: ガラス入り耐熱樹脂 UL 94V-0 色: 黒 HOUSING: G.F. HEAT RESISTANT PLASTIC UL94V-0 COLOR: BLACK ターミナル: りん青銅 t0.3 TERMINAL: PHOSPHOR BRONZE t0.3 メッキ仕様 接点部: ニッケル下地金メッキ PLATING CONTACT AREA: GOLD OVER NICKEL 結線部: ニッケル下地錫メッキ WIRE TERMINATION AREA: TIN OVER NICKEL
②	カバーA COVER A	54181-0616	1	カバーA: ガラス入りポリカーボネイト樹脂 COVER A: POLYCARBONATE G.F. UL 94V-0 色: 黒 UL94V-0 COLOR: BLACK スプリングラッチ: ステンレス鋼 t0.4 SPRING LATCH: STAINLESS STEEL t0.4
③	カバーB COVER B	54182-0606	1	ガラス入りポリカーボネイト樹脂 UL 94V-0 色: 黒 POLYCARBONATE G.F. UL94V-0 COLOR: BLACK
④	シェル カバー SHELL COVER	58299-0626	1	鋼 t0.4 STEEL t0.4
⑤	シェル ボディ SHELL BODY	58300-0626	1	メッキ仕様: ニッケル下地、錫メッキ PLATING: NICKEL BASE, TIN PLATING
⑥	ケーブルクランプ CABLE CLAMP	58303-0000	1	ステンレス鋼 STAINLESS STEEL
⑦	十字穴付きナベ小ネジ CROSS RECESSED PAN HEAD MACHINE SCREW	59832-0009	2	黄銅(ネジサイズ: M2X4) BRASS (SCREW SIZE: M2X4)

## NOTES:


本製品は55100-0600の鉛フリー品である  
THIS PRODUCT IS LEAD FREE OF 55100-0600.



COVER A





COVER B



SHELL COVER

BLACK COVER COLOR	POLY BAG PACKAGE METHOD	55100-0671 MATERIAL No.	55100-***1 MODEL No.
----------------------	----------------------------	----------------------------	-------------------------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		molex	
DIMENSION UNITS mm	SCALE NTS	CURRENT REV DESC:	
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 627599 DRWN: KTAKEUCHI01 2019/10/02 CHK'D: TKON 2019/11/19 APPR: ASHIMOTSU 2019/11/19	
ANGULAR TOL $\pm$ °		INITIAL REVISION: DRWN: HKAWABATA 2004/05/21 APPR: MSASAO 2004/05/21	
4 PLACES	$\pm$	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
3 PLACES	$\pm$	THIRD ANGLE PROJECTION	
2 PLACES	$\pm$	DRAWING	SERIES
1 PLACE	$\pm$	A3-SIZE	55100
0 PLACES	$\pm$	SEE TABLE	CUSTOMER GENERAL MARKET
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NUMBER	SHEET NUMBER 2 OF 2
PRODUCT CUSTOMER DRAWING		DOCUMENT NUMBER SD-55100-004	DOC TYPE PSD DOC PART 001 REVISION C



B DIMENSIONS IN METRIC DO NOT SCALE DRAWING : MM

A DWG. NO. SD-58303-0000

注記 NOTES.	1. 材質 MATERIAL STAINLESS STEEL	2. 適合シエリレカ/ /ー 。 58299-0600 58299-0800 APPLICABLE SHELL COVER : 58299-0600 58299-0800 , 58302-0600 58302-0800	REVISE ONLY ON CAD SYSTEM TITLE 名称 TITLE
角 度 ANGLE $\pm 3^\circ$	30 $\overset{\text{上}}{\text{OVER}}$ $\pm 0.3$ 10 $\overset{\text{上}}{\text{OVER}}$ 30 $\overset{\text{未達}}{\text{UNDER}}$ $\pm 0.25$ 10 $\overset{\text{未達}}{\text{UNDER}}$ $\pm 0.2$	仕上 <sup>J7</sup> FINISH	REVISE ONLY ON CAD SYSTEM TITLE
一般公差 GENERAL TOLERANCES		注記参照 SEE NOTES	REVISE ONLY ON CAD SYSTEM TITLE
		STAINLESS STEEL	REVISE ONLY ON CAD SYSTEM TITLE
		適用電線範囲 WIRE RANGE	REVISE ONLY ON CAD SYSTEM TITLE
		適用外範囲 INS. RANGE	REVISE ONLY ON CAD SYSTEM TITLE
		DRAWN BY <u>J.Y.I.</u> 96/12/19 CHK'D BY <u>Y.Q.Z.</u> 97/08/20	REVISE ONLY ON CAD SYSTEM TITLE
		APPR'D BY <u>Mizawo</u> 96/12/19 DATE <u>1996/12/19</u>	REVISE ONLY ON CAD SYSTEM TITLE
記号 LTR	変更内容 REVISION RECORD	尺度 SCALE	REVISE ONLY ON CAD SYSTEM TITLE
	DR. C.H.	4 - 1	REVISE ONLY ON CAD SYSTEM TITLE

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX/JAPAN AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

本図面は日本モレックス(株)の所有する情報を持むもので当社の許可なく複製を禁ずる。

SD-58303.DCN

EN-0(C-032)MX-1-33