

Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID COLOR, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, lettering field size: 60 x 15 mm, Number of individual labels: 4

Your advantages

- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK LED
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial Data

Item number	0827647
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to Order (non-returnable)
Sales Key	B12
Product Key	BG2417
Catalog Page	Page 301 (C-3-2019)
GTIN	4046356446587
Weight per Piece (including packing)	9.58 g
Weight per Piece (excluding packing)	9.58 g
Customs tariff number	39269097
Country of origin	PL

Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Technical Data

Product properties

Product type	Device marking
Marking	
Number of individual labels	4
Number of individual labels per row	1
Marking technology	
Device	5147999 BLUEMARK CLED
Printability	UV LED technology

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Mounting

Mounting type	insert
---------------	--------

Material specifications

Color	silver
RoHS compliant	Yes
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen
Silicone-free	yes
Halogen-free	Yes

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	60 mm
Length	15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Classifications

ECLASS

ECLASS-9.0	27400629
ECLASS-10.0.1	27400629
ECLASS-11.0	27281106

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Accessories

Marker carriers

Marker carriers - CARRIER-EMP (60X15) - 0827453

<https://www.phoenixcontact.com/us/products/0827453>

Marker carriers, black, unlabeled, mounting type: screw, rivet, lettering field size:
60 x 15 mm



Marker carriers

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

<https://www.phoenixcontact.com/us/products/0829366>

Profile, for screwing or riveting, 1000 mm long, for accommodating UC und US
materials, height: 15 mm



Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Marker carriers

Marker carriers - CARRIER-EMP (1000X15) TR - 0829530

<https://www.phoenixcontact.com/us/products/0829530>



Marker carriers, transparent, unlabeled, mounting type: screw, rivet, lettering
field size: 1000 x 15 mm

Marker carriers

Marker carriers - CARRIER/L-EMP (1000X15) TR - 0829560

<https://www.phoenixcontact.com/us/products/0829560>



Profile, self-adhesive, 1000 mm long, for accommodating UC-,/US-, LS-, and
EMT (EX15)R material, 15 mm height

Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Marker carriers

Marker carriers - CARRIER/L-EMP (1000X15) GY - 0829559

<https://www.phoenixcontact.com/us/products/0829559>



Profile, self-adhesive, 1000 mm long, for accommodating UC-,/US-, LS-, and EMT (EX15)R material, 15 mm height

Magazine

Magazine - P1 UC-MAG 6 - 5146121

<https://www.phoenixcontact.com/us/products/5146121>



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-EMP..., UC-EMLP...

Snap-in markers - UC-EMP (60X15) SR



0827647

<https://www.phoenixcontact.com/us/products/0827647>

Ink cartridge

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662

<https://www.phoenixcontact.com/us/products/5146662>

Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge



Ink cartridge

Ink cartridge - BLUEMARK FLUID-CARTRIDGE - 5147421

<https://www.phoenixcontact.com/us/products/5147421>

Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge



Snap-in markers - UC-EMP (60X15) SR

0827647

<https://www.phoenixcontact.com/us/products/0827647>



Ink cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345

<https://www.phoenixcontact.com/us/products/1044345>



Replacement UV fluid, 23 ml, color: black

Ink cartridge

Ink cartridge - BM ID-CARTR. CY - 1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan

Snap-in markers - UC-EMP (60X15) SR

0827647

<https://www.phoenixcontact.com/us/products/0827647>



Ink cartridge

Ink cartridge - BM ID-CARTR. YE - 1044348

<https://www.phoenixcontact.com/us/products/1044348>



Replacement UV fluid, 23 ml, color: yellow

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com