





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/08/10	
A		REVISED DIM.	5/30/11	
B		REVISED SPEC.	12/22/11	
C		REVISED SPEC.	7/13/15	AV/KW



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Shell: Brass, nickel plated

Plating:

Gold over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails

Electrical:

Operating voltage: 30 VAC max.

Current rating: 1.5 Amp max @ 250V AC.

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

UNIVERSAL SERIAL BUS

SINGLE PORT, VERTICAL, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES Holes X ± .10 XX ± .020 XXX ± .015				DATE			
APPROVALS				DATE			
DRAWN	DY	4/08/10					
CHECKED							
APPROVED							
TITLE				SIZE			
				PART NO.			
				USB-A-S-VT-HT			
				REV.			
				C			