Specifications



Photo is representative





Eaton MIC-6

Eaton Bussmann series MIC fuse, Fast acting, Midget fuse, Control circuits, PLC circuits, Electronic circuits, 6 A, Non-indicating, 200 AIC at 250 Vac, Nickel-plated bronze endcap, Fiber tube, Standard, 250 V

General specifications

PRODUCT NAME	Eaton Bussmann series MIC fuse
CATALOG NUMBER	MIC-6
UPC	051712183932
PRODUCT LENGTH/DEPTH	1.813 in
PRODUCT HEIGHT	0.47 in
PRODUCT WIDTH	0.47 in
PRODUCT WEIGHT	1.5 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked
PRODUCT TYPE	Fuse

Powering Business Worldwide

Downloaded from Arrow.com.

Electrical rating

AMPERAGE RATING	6 A
INTERRUPT RATING	200 AIC at 250 Vac
VOLTAGE RATING	250 V

Physical details

MATERIAL	Fiber tube Nickel-plated bronze endcap
PACKAGING TYPE	Standard

General information

FUSE INDICATOR	Non-indicating

Resources

CATALOGS	MIC-6~BUSS MIDGET FUSE Bussmann series complete full line catalog no. 1007
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - MIC-6

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.