





REV.	DATE	DESCRIPTION
NC	04/29/99	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIM'S.



- NOTE:
1. CRIMPED FERRULE
HEX. CRIMP SIZE .128"
 2. CONTACT PIN TO SOLDER.

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.6 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
7						DRAWN	G.R.S.	05/01/04							
6						CHECKED									
5	FERRULE	COPPER	GOLD	1		ISSUED				PART DESCRIPTION					
4	BARREL	BRASS	GOLD	1		SHEET	1 OF 1			MMCX CRIMP JACK (FOR RG-174/U,188A/U,316/U)					
3	CONTACT PIN	BER. COPPER	GOLD	1	DESCRIPTION	PART NO.									
2	INSULATOR	TEFLON	NATURAL	1		262118									
1	BODY	BRASS	GOLD	1		DWG. NO. 262118.DWG									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE		C:/262/262118.DWG		REV.	A	SIZE	A	SCALE	NA