



Part Number : [640010200](#)
Product Description : PremiumGrade Hand Crimp
Tool for Insulkrimp Quick Disconnect Terminals, 22-10
AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand
Tools
Engineering Number : RHT-1991



Documents & Resources

Tooling Specifications

- [ATS-640010200-001.pdf](#)
- [TM-640160065-001.pdf](#)
- [TM-640160065CN-001.pdf](#)
- [TM-640160065SP-001.pdf](#)
- [TM-640160065IT-001.pdf](#)
- [TM-640160065JP-001.pdf](#)
- [TM-640160065KR-001.pdf](#)
- [TM-640160065MY-001.pdf](#)
- [TM-640160065PL-001.pdf](#)
- [TM-640160065RU-001.pdf](#)
- [TM-640160065SK-001.pdf](#)
- [TM-640160065TH-001.pdf](#)
- [TM-640160065VN-001.pdf](#)
- [TM-640160065TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant

Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 22-10 AWG
Comments	ServiceGrade Hand Tool 640160037; Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054219881

Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
---------------------	--

Physical

Net Weight	643.700/zg
------------	------------

Applicable Parts

Description	Part Number
Avikrimp Fully Insulated Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Carton, Tab 6.35 x 0.81mm	<u>190020044</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.51mm	<u>190170001</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.81mm	<u>190170005</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 4.75 x 0.51mm	<u>190170007</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 4.75 x 0.81mm	<u>190170008</u>

InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190170014</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 5.21 x 0.51mm	<u>190170018</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 2.79 x 0.51mm	<u>190170023</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 2.79 x 0.81mm	<u>190170028</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 4.75 x 0.51mm	<u>190170031</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 4.75 x 0.81mm	<u>190170032</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190170037</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 5.21 x 0.51mm	<u>190170043</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 5.21 x 0.81mm	<u>190170044</u>
InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190170047</u>
Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.51mm	<u>190190001</u>
Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 2.79 x 0.81mm	<u>190190004</u>
Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 4.75 x 0.51mm	<u>190190006</u>
Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 4.75 x 0.81mm	<u>190190008</u>

Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190190012</u>
Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 5.21 x 0.51mm	<u>190190014</u>
Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 5.21 x 0.81mm	<u>190190015</u>
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 2.79 x 0.51mm	<u>190190022</u>
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 2.79 x 0.81mm	<u>190190025</u>
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 4.75 x 0.51mm	<u>190190027</u>
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 4.75 x 0.81mm	<u>190190028</u>
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190190031</u>
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 5.21 x 0.51mm	<u>190190034</u>
Avikrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 5.21 x 0.81mm	<u>190190035</u>
Avikrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	<u>190190037</u>
Quixon Quick Disconnect, InsulKrimp Style, Female, Partially Insulated Red, 22-18 AWG, Loose	<u>192740002</u>
Quixon Quick Disconnect, InsulKrimp Style, Female, Partially Insulated Blue, 16-14 AWG, Loose	<u>192740005</u>
Quixon Quick Disconnect, Avikrimp Style, Female, Partially Insulated Red, 22-18 AWG, Loose	<u>192750002</u>

Quixon Quick Disconnect, Avikrimp Style, Female, Partially Insulated Blue, 16-14 AWG, Loose	<u>192750005</u>
Quixon Quick Disconnect, Avikrimp Style, Female, Fully Insulated Yellow, 12-10 AWG, Loose	<u>192770008</u>
Avikrimp Fully Insulated Quick Disconnect, Female, for 12-10 AWG Wire, Box	<u>196060005</u>

This document was generated on Sep 22, 2025