



- Notes on operating the antenna with WAGO EnOcean radio receivers:
- The antenna is to be mounted on a plate measuring at least 1 x 1 inches (25 x 25 cm).
 - The distance of interfering sources to the antenna and antenna line must be at least 30cm and the free space between the antenna and the next wall must be at least 35cm.
 - The antenna cable should, under no circumstances, be bent sharply, since irreversible damage may result to the antenna line (RG174 bend radius > 15mm).

Technical data		
Radio technology		Bluetooth® WLAN
Frequency band		2400 MHz ... 2485 MHz
Gain		2 dBi

Mechanical data		
Connector		SMA right angle plug
Length of connection cable		2.5 m

Material data		
Fire load		0 MJ
Weight		92 g

Commercial data		
Product Group		27 (special components I/O)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4045454636470
Customs tariff number		85177100000
End of Sale		2023-11-01
End of Production		2023-12-22
End of Delivery		2023-12-23
End of Service and Repair		2023-12-24



Product classification		
UNSPSC		43221730
eCl@ss 10.0		19-07-91-01
eCl@ss 9.0		19-07-01-05
ETIM 9.0		EC001698
ETIM 8.0		EC001698
ECCN		NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 758-912	

Documentation

System Description			Bid Text	
Radio Technology – General Product Information	pdf 493.44 KB		758-912	09.10.2017
			doc 24.50 KB	
			758-912	19.02.2019
			xml 3.62 KB	

CAD/CAE-Data

CAE data	
WSCAD Universe 758-912	