

Han 24B HTE M40 PFT CL



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 024 1142
Specification	Han 24B HTE M40 PFT CL
HARTING eCatalogue	https://b2b.harting.com/19300241142

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Panel feed through housing
Type	High construction

Version

Size	24 B
Version	Top entry
Cable entry	1x M40
Locking type	Central locking lever (on the hood)
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

Specifications and approvals

CE	Yes
----	-----

Commercial data

Packaging size	1
Net weight	394 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors