

CT3189

DMM Probe Alligator Clip

Datasheet

Insulated Alligator Clip with thread for assembly to Multimeter fused...

Description

Insulated Alligator Clip with thread for assembly to Digital Multimeter fused probe bodies.

- Materials: Body: Polyamide (Nylon); Contact: Brass, Nickel Plt.
- Available in pair Red and Black model CT3208



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT III
Current Max	20 A
Resistance Max	20 mohm
Temperature (degrees)	-20 to +80 degC
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

