



[Products](#) > [Lenses](#) > [Fixed Focal Lenses](#)

## Kowa Lens LM12HC F1.4 f12.5mm 1" - Lens

Kowa C-mount lens with a fixed focal length of 12.5 mm and an aperture range from F1.4 - F16.

This is a 1" lens for sensors with high resolution.

Net list price **349.00 EUR**

[Buy now](#)

[Request individual quote](#)



### Specifications

### Documents

### Cameras

#### General Information

|                                                                                                  |                   |
|--------------------------------------------------------------------------------------------------|-------------------|
| Order Number                                                                                     | 2000034589        |
| Net list price                                                                                   | 349.00 EUR        |
| For larger quantities and individual prices, please use the request cart.                        |                   |
| Est. Lead Time                                                                                   | approx. 4-5 weeks |
| Estimated lead times may vary. Please ask for the current availability and use the request cart. |                   |
| Destination                                                                                      | Egypt             |
| Accessory Type                                                                                   | Lens              |
| Manufacturer                                                                                     | Kowa              |

#### Lens Data

|                       |              |
|-----------------------|--------------|
| Focal Length          | 12.5 mm      |
| Lens Mount            | C-mount      |
| Iris                  | F1.4 - F16.0 |
| Iris Type             | manual       |
| IR Cut Filter         | no           |
| Pixel Pitch           | 5,50 µm      |
| Sensor Format         | 1"           |
| Min. Working Distance | 300 mm       |

[f](#) share

[t](#) tweet

[in](#) share

[✉](#) mail

[i](#)

#### Contact & Support

- [Sales Contact >](#)
- [Support Contact >](#)
- [Aftersales Services >](#)
- [Product Documentation >](#)

#### About Basler

- [Jobs at Basler >](#)
- [News and Press >](#)
- [Tradeshows and Events >](#)

#### Investor Relations

- [Share >](#)
- [Financial Information >](#)
- [Financial Calendar >](#)
- [Corporate Governance >](#)
- [Contact Investor Relations >](#)

#### Information

- [Legal Info >](#)
- [Data Protection Declaration >](#)
- [Legal Notice >](#)
- [Terms and Conditions >](#)
- [Sitemap >](#)
- [Glossary >](#)
- [Contact >](#)
- [Driving Directions >](#)

#### Webshop

Find and buy Basler products in our new Basler Webshop.

[Visit Webshop](#)

#### eNewsletter

Regular updates on events and product innovations:

[Subscribe](#)

#### Basler on Social Media

Keep in touch with us via the social networks:

