



**Part Number :** [191930307](#)

**Product Description :** VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton

**Series Number :** 19193

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Part Number :** G-375-38

---

## Documents and Resources

### Drawings

[191930307 sd.pdf](#)

[191930307 stp.zip](#)


### Specifications

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:b984cbc6-acbb-4d3c-be53-51cb15970fc3
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 2 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755051568

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	12.928/g
Packaging Type	Carton
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	13.35mm max.
Wire Size (AWG)	2
Wire Size mm <sup>2</sup>	35.00

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900010</u>
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	<u>192940008</u>
Square "DIN" style dies for 2 AWG	<u>640037970</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>

---

This document was generated on Dec 26, 2025