

PDIGTR

APC Surge Module for Digital Phone Line (T1, CSU, DSU, ISDN, DLL), Replaceable, 1U, for PRM4, PRM24



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Colour	Black
Depth	6.9 cm
Height	4.4 cm
Net weight	0.02 kg
Width	1.9 cm

Output

Number of power socket outlets	1
--------------------------------	---

Conformance

Product certifications	CUL recognized CE VDE
Standards	UL 497A

Environmental

Ambient air temperature for operation	-15...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...3048.00 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Surge Protection and Filtering

Data line protected	1-8
Response time	1 ns common mode
Peak current	0.25 kA common mode 0.2 kA normal mode
Data line protection	RJ45 ISDN/T1 protection

Packing Units

Package 1 Weight	0.05 kg
Package 1 Height	9.9 cm
Package 1 width	3.3 cm
Package 1 Length	9.5 cm
SCC14	30731304203378
Number of Units in Package 2	96
Package 2 Weight	6.80 kg
Package 2 Height	206.38 mm
Package 2 width	412.75 mm
Package 2 Length	638.18 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	Lifetime
----------	----------