

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0526741691](#)
Status: **Active**
Description: 2.00mm Pitch LCD Pin Connector, Black, 16 Circuits

Documents:

[3D Model](#) [Product Specification PS-52674-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Other Sockets
Series [52674](#)
Component Type Socket
Product Name 2.0 LCD Socket
UPC 800753343917

Physical

Circuits (Loaded) 16
Circuits (maximum) 16
Color - Resin Black
Durability (mating cycles max) 10
Entry Angle Vertical (Top Entry)
Keying to Mating Part N/A
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1592.800/mg
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tube
Pitch - Mating Interface 2.00mm
Pitch - Termination Interface 2.00mm
Plating min - Mating 0.914µm
Plating min - Termination 0.914µm
Temperature Range - Operating -40° to +100°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 1.0A
Voltage - Maximum 125V


Solder Process Data

Duration at Max. Process Temperature (seconds) 025
Lead-freeProcess Capability SMC&WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Product Specification PS-52674-002
Sales Drawing SD-52674-XX21, SD-52674-XX91



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS Green Image
ELV Compliant
RoHS Phthalates Not Contained

Search Parts in this Series

[52674 Series](#)

Mates With

LCD Pin 0.30 x 0.50mm (.012 x .020")

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION