

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1203410075](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Micro-Change M12 CAT6A Front Panel-Mount Receptacle, 8 Poles, Female (Straight), 0.0185m (.728") Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-120341-075 \(PDF\)](#)

General
Product Family Industrial Receptacles
Series [120341](#)
IP Rating IP67
Overview [Brad Industrial Ethernet Solutions](#)
Performance Category 6A
Product Name Micro-Change (M12) Cat6A
Type PCB Mount
UPC 884982163355

Physical
Coupling Type Internal Thread
Gender Female
Keyway X-coded
Length 0.0185m
Material - Component Nickel-plated Brass
Mounting Thread Size M12 x 1.0
Net Weight 9.391/g
Orientation Straight
Panel Mount Front
Poles 8
Temperature Range - Operating -40°C to +70°C
Wire Size AWG N/A
Wire/Cable Type N/A

Electrical
Current - Maximum per Contact 0.5A
Voltage - Maximum 48V

Material Info
Engineering Number ER2D2U303

Reference - Drawing Numbers
Packaging Specification PK-120341-075
Sales Drawing SD-120341-075



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/108/2014 (17 Dec 2014)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120341](#) Series

Mates With
[120341](#) Micro-Change CAT6A Cable Assemblies

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION