



Color: white

Technical data	
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	500 pcs/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Height	20 mm
Width	25 mm
Depth	0.17 mm
Marking surface	25 x 11 mm

Mechanical data	
Mounting type	Mounting with cable ties
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	white
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	129.5 g
Fire load	0 MJ



Environmental requirements		
Ambient temperature (storage)		+10 ... +21 °C
Ambient temperature (operation)		-40 ... +150 °C
Relative humidity		40 ... 50 %

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4050821688648
Customs tariff number		39269097900

Product classification		
UNSPSC		55121612
eCl@ss 10.0		27-40-04-01
eCl@ss 9.0		27-40-06-29
ETIM 9.0		EC001530
ETIM 8.0		EC001530
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 211-835

↓

Documentation

Operating Instructions

211-835 Information on printing material

1

28.08.2020

pdf

1380.62 KB

↓