

BPDR000707401 00M00

Search by : Part Number Characteristics Cross reference



MP


Closed Magnetic Circuit Type

Series Pdf

Product detail	
L(mm) ±	6.7±0.3
W(mm) ±	6.7±0.3
T(mm) ±	4.0Max.
Inductance(uH)	10
Tolerance(±%)	20
Test Frequency	100kHZ,0.25V
RDC(Ω)Max	0.038
Isat(A)Max	2
Irms(A)Typ	2
Operating Temperature	－40℃～125℃ (Including self - temperature rise)

Part Numbering Dimensions Packing Recommended Pattern Electrical Characteristics

Downloaded from Arrow.com.



Downloaded from Arrow.com.

Media Center
New Products
Events
Product Notices

Contact Us

Contact Info
Contact Form
Join Chilisin

Terms of Use
Privacy policy
Sitemap



Inductor

Resistor

Powder

Copyrights © 2018. Chilisin. All rights reserved.

Downloaded from Arrow.com.