

CPU Coolers



Model Names	Special CPU Cooler		Pentium 4 LGA775		Pentium 4 Socket 478
	1750000400	1750000282	1750000332	1750000334	1750000242
Minimum Chassis Height	2U	2U	2U	4U	1U
CPU Package	Only for PCE-5120	Only for PCE-7210	Intel Pentium 4 LGA775	Intel Pentium 4 LGA775	Intel Pentium 4 Socket 478
CPU Speed	up to 3.4 GHz (90 nm, 110 W, L2: 1 MB)	up to 3.8 GHz (90 nm, 115 W, L2: 1 MB)	up to 3.8 GHz (90 nm, 115 W, L2: 1 MB)	up to 3.8 GHz (90 nm, 115 W, L2: 1 MB)	up to 2.5 GHz (0.13 micron, 61 W, L2: 512 KB)
Heat Sink Material	Copper	Copper	Copper	Aluminum fins & copper heart	Copper
Fan Speed	5,400 +- 10% RPM	6,800 +- 10% RPM	5,300 +- 10% RPM	4,500 +- 10% RPM	3,800 +- 10% RPM
Weight	672 g	624 g	560 g	550 g	335 g
Dimension	89 x 74 x 51 mm	82 x 58 x 65.5 mm	80 x 80 x 55 mm	110 x 110 x 67 mm	88.5 x 62 x 29.9 mm



Model Names	Pentium 4 Socket 478		Pentium III	Intel MMX	
	1750000432	1750000257	1759254100	1759200100	1759212600
Minimum Chassis Height	1U	2U	1U	1U	2U
CPU Package	Intel Pentium 4 Socket 478	Intel Pentium 4 Socket 478	Intel Pentium III FC-PGA II	Intel MMX	Intel MMX
CPU Speed	up to 2.8 GHz (0.13 micron, 70 W, L2: 512 KB)	up to 3.2 GHz (90 nm, 89 W, L2: 1 MB)	up to 1.26 GHz (Tualatin)	-	-
Heat Sink Material	Copper	Copper	Aluminum	Aluminum	Aluminum
Fan Speed	4,800 +- 10% RPM	4,500 +- 10% RPM	4,700 +- 10% RPM	5,000 +- 10% RPM	5,000 +- 10% RPM
Weight	478 g	565 g	101 g	77 g	77 g
Dimension	93 x 77 x 27 mm	83 x 69 x 55.5 mm	59 x 57x 28 mm	52 x 52x 29 mm	52 x 52x 42 mm