



C2G

**Discontinued - 14ft (4.25m) Cat5E Non-Booted Unshielded (UTP) Ethernet Network Patch Cable Multipack (100-Pack) - Blue**  
Part No. CG-24380



For fast Ethernet computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat5e TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code your network installation.

## Features & Benefits

Designed for network adapters, hubs, switches, routers, HDBaseT applications and more

Meets all Cat5e TIA/EIA requirements for supporting a wide variety of applications

CMG rated jacket for in-wall installations

Supports 1 Gigabit networks up to 328ft for fast data transmission and maximum performance

Constructed with unshielded twisted pair (UTP) wires, designed to counter EMI, RFI, and crosstalk

## Specifications

### General Info

Product Line	C2G	Color	Blue
UPC Number	757120243809	Country Of Origin	China
Application Sector	Commercial, Industrial, Residential	Type	Cable

### Dimensions

Product Length US	14.0 FT	Cable Length	14 ft
Outside Diameter	5.2 mm		

### Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Application	Cat5e
Wire Gauge	24 AWG	Shielded/Unshielded Cable	Unshielded
Conductor	4-Pair Twisted	Shield Type	UTP
Cable Type	Ethernet Patch Cable	Jacket Rating	Standard / Non-Rated
Cable Diameter	5.3 mm	Connector Type	Non-booted
Indoor/Outdoor	Indoor	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male	Bandwidth	350 MHz
Insulation Material	HDPE (High-density Polyethylene)		