


Specifications:

Material: Copper Tube, Tin Plated

Operating Temperature Range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.14 -0.00	Dim.W ±0.20	Wire Range AWG mm²
3060-06014G	GRAY	6.0	10.0	0.70	1.60	26AWG
3060-08014G	GRAY	8.0	12.0			0.14mm²
Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.25 -0.00	Dim.W ±0.20	Wire Range AWG mm²
3060-06025G	LIGHT BLUE	6.0	10.0	0.75	1.90	24AWG
3060-08025G	LIGHT BLUE	8.0	12.0			0.25mm²
Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.14 -0.00	Dim.W ±0.20	Wire Range AWG mm²
3060-06034G	TUR-QUOISE	6.0	10.0	0.80	1.90	22AWG
3060-08034G	TUR-QUOISE	8.0	12.0			0.34mm²
Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.14 -0.00	Dim.W ±0.20	Wire Range AWG mm²
3060-06050G	ORANGE	6.0	12.0	1.00	2.60	20AWG 0.5mm²
3060-06050D	WHITE					
3060-08050G	ORANGE	8.0	14.0			
3060-08050D	WHITE					
3060-10050D	WHITE	10.0	16.0			
Part No	Color	Dim.F ±0.40	Dim.L ±1.50	Dim.C +0.14 -0.00	Dim.W ±0.20	Wire Range AWG mm²
3060-06075G	WHITE	6.0	12.0	1.20	2.80	18AWG 0.75mm²
3060-06075D	GRAY					
3060-08075F	BLUE	8.0	14.0			
3060-08075G	WHITE					
3060-08075D	GRAY					
3060-10075D	GRAY	10.0	16.0			
3060-12075D	GRAY	12.0	18.0			

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE:	CnC Tech Industrial Cable and Connector Technology	
				JAMIE	.X = ± 0.20 .XX = ± 0.15		
				CHECKED:	UNIT: MM	DESCRIPTION:	SIZE
				JERRY	SCALE: 1:1		
A	09-JAN-2023			APPROVAL:	SHEET: 1 / 1	PART NO:	A4
REV	DATE	FILE	BY	RORY	PROJECTION:		