
C2G

C2G
DISCONTINUED: 25ft (7.6m) Cat6 Snagless UTP Unshielded Ethernet Network Patch Cable - Gray
Part No. CG-22816



100% manufactured and tested within the United States, this cable meets the stringent requirements for anyone who needs to procure products exclusively manufactured in the USA. For voice/data/video distribution, this cable will handle bandwidth-intensive applications. Meets all Cat5E TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL) .

Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point.

Constructed from high quality cable and a shortened body plug, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

- Designed for network adapters, hubs, switches, routers, HDBaseT applications and more
- Supports 10 Gigabit networks up to 180ft for fast data transmission and maximum performance and supports 1 Gigabit up to 328ft
- Meets all Cat6 TIA/EIA requirements for supporting a wide variety of applications
- Constructed with unshielded twisted pair (UTP) wires, designed to counter EMI, RFI, and crosstalk
- Snagless connector design for high density environments and protecting the RJ-45 connector's lock

Specifications

General Info

Product Line	C2G	Color	Gray
UPC Number	757120228165	Country Of Origin	China
Application Sector	Residential, Commercial, Industrial	Type	Cable

Dimensions

Cable Length	25 ft

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Cable Type	Ethernet Patch Cable, Snagless, Unshielded (UTP)
Jacket Rating	Standard Non-Rated	Adapter Rear	RJ-45 Male

Downloaded from Arrow.com.

Adapter Front	RJ-45 Male

Downloaded from Arrow.com.