




REV.	DATE	DESCRIPTION
A	02/08/03	UPDATE DRAWING FORMAT



PCB MOUNTING HOLES

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex										
8						DRAWN	G.R.S.						02/08/03					
7						CHECKED			PART DESCRIPTION MCX P.C. BOARD RECEPTACLE JACK (3.94 [.155”] LEGS – SHORT BODY)									
6						ISSUED												
5						SHEET	1 OF 1		PART NO. 252105									
4																		
3	CONTACT PIN	BER. COPPER	GOLD	1		CAD FILE		C:/225/252105..DWG		DWG. NO.		252105.DWG	REV.	A	SIZE	A	SCALE	NA
2	INSULATOR	TEFLON	NATURAL	1														
1	BODY	BRASS	GOLD	1														
	DESCRIPTION	MATERIAL	FINISH	QTY														