



Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Copper

By Burndy
Catalog # [MRC840](#)

Mechanical Rotating, #8-4/0 Copper



Features

- Spring loaded mechanism locks die wheel into position
- Press mechanism to release
- Rotating die wheel color coded marked with AWG sizes
- Steel jaws

Application

Crimping

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	EX

Conductor

Crimping Ranges	Copper: #8 AWG- #4/0 AWG
-----------------	--------------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in

Length	26 in
Width	8 in
Weight	8.25 lb.
Height	1.5 in
Dimensions	26 in x 8 in x 1.5 in

General

Sub Brand	HYTOOL
Trade Name	HYTOOL™
Application - For Use On	Copper Terminals and Splices
UPC 12 Digit	781810192504
UPC 14 Digit GTIN	00781810192504
Tool Type	Mechanical Rotating Crimper
UPC	781810192504
Die Type	Rotating Die Wheel

Logistics

Package Contents	Tool only
Minimum Pack Quantity	1
Carton Quantity	5

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)