

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Shielded Miniature Circular DIN Connectors

Product Highlights:

- ? Connector
- ? Number of Positions = 6
- ? PCB Mount Angle = Vertical
- ? Shielded
- ? Without Front Panel Grounding

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

- ? RECEPTACLE ASSEMBLY, 6 POSN, LOW FLANGE, UNSHIELDED,...
(TIF, English)

? None Available

? None Available

? None Available

? None Available

? None Available

Additional Information:

- ## ? Product Line Information

Related Products:

- ## ? Tooling

List all Documents

Product Type Features:

- ? Product Type = Connector
 ? Number of Positions = 6
 ? Shielded = Yes
 ? PCB Mount Angle = Vertical
 ? Front Panel Grounding = Without
 ? Front Panel Screw -Down = Without
 ? PCB Retention Feature = No
 ? Gender = Receptacle
 ? Stacked = No
 ? Color Code = None
 ? PCB Mount Style = Thru Hole
 ? Inner Shield Material = Copper Alloy

? Grounding Clips = Without
? Solder Tail Contact Plating = Tin

? Inner Shield Plating = Tin over Nickel

Contact Related Features:

- ? Contact Mating Area Plating Material = Gold (15)
- ? Contact Material = Copper Alloy
- ? Contact Underplating = Nickel (50)

Housing Related Features:

- ? Housing Material = Thermoplastic
 ? Housing Flammability Rating = UL 94V -0
 ? Housing Color = Black

Configuration Related Features:

- ? SPDIF Connector = Without

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = AMP