

Specification Sheet

Part Number: MP2M5.NN3P



Mounting plates allow multiple bundles to run parallel.

The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.

Cable Tie Mounting Plate, 0.50" x 3.00", T18-T50 Cable Ties, #10 (M5) Screw, PA66, Natural, 100/pkg

Article Number	154-00300
Type	MP2M5
Color	Natural (NA)
Quantity Per	pack
Product Description	HellermannTyton mounting plates allow multiple cable to be run in parallel. The mount is secured with two screws and the cables are attached to the plate by using a cable tie through any of the available slots.
Short Description	Cable Tie Mounting Plate, 0.50" x 3.00", T18-T50 Cable Ties, #10 (M5) Screw, PA66, Natural, 100/pkg
Global Part Name	MP2M5-PA66-NA

Length L (Imperial)	3.0
Length L (Metric)	76.2
Fixation Method	Screw Mount
Width W (Imperial)	0.5
Width W (Metric)	12.7
Cable Ties	T18 - T50
Height H (Imperial)	0.125
Height H (Metric)	3.2
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.2
Mounting Hole Diameter D (Imperial)	0.2
Mounting Hole Diameter D (Metric)	5.1 mm
Mounting Hole Diameter D Max (Metric)	5.1
Mounting Hole Centers (Imperial)	1.25
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)