

## Base strip - MSTBV 2,5/15-GF-5,08 AU - 1805494

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 15, Pitch: 5.08 mm, Color: green, Contact surface: Gold, Mounting: Wave soldering



### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	500 STK
GTIN	 4 055626 388502
GTIN	4055626388502
Weight per Piece (excluding packing)	8.000 g
Custom tariff number	85366930
Country of origin	Germany

### Technical data

#### Dimensions

Length	8.6 mm
Pitch	5.08 mm
Dimension a	71.12 mm
Width	86.36 mm
Constructional height	12 mm
Height	15.9 mm
Length of the solder pin	3.9 mm
Pin dimensions	1 x 1 mm
Hole diameter	1.4 mm

#### General

Insulating material group	IIIa
Rated voltage (III/2)	320 V
Nominal current $I_N$	12 A
Flammability rating according to UL 94	V0

## Base strip - MSTBV 2,5/15-GF-5,08 AU - 1805494

### Technical data

#### General

Color	green
Number of positions	15

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"