



Part Number : [5600850101](#)
Product Description : DuraClik Crimp Terminal,
Female, 26-22 AWG, Tin (Sn) Plating, Reel
Series Number : 560085
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

- [5600850101_sd.pdf](#)
- [PK-560085-001-001.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [AS-560085-001-JP-001.pdf](#)
- [PS-502351-001-001.pdf \(Tin Plating\)](#)

Tooling Specifications

- [571753710ATS-000.pdf](#)
- [571753710ATS-J-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	560085
Description	DuraClik Crimp Terminal, Female, 26-22 AWG, Tin (Sn) Plating, Reel
Application	Automotive, Power, Signal, Wire-to-Board
Product Name	DuraClik
UPC	887191151892

Electrical

Voltage - Maximum	125V
-------------------	------

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.022/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	1.40mm
Wire Size (AWG)	22, 24, 26
Wire Size mm ²	0.34

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
DuraClik Single Row Receptacle Housings	<u>502351</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>11030043</u>
FineAdjust Applicator for 2.00mm Pitch Wire-to-Board Crimp Receptacle Terminal and SMEC Crimp Receptacle Terminals, 26-22 AWG and AVSS 0.3 Wires	<u>2037021900</u>
PremiumGrade Hand Crimp Tool for Micro-Latch, DuraClik, and Servo Motor Encoder Female Terminals, 26-22 AWG	<u>638235100</u>

This document was generated on May 19, 2026