

Mallory Sonalert Products, Inc.		Part #:		ZA016MDMT2	
Sales Outline Drawing		Revision:		F	
Specifications:					
Sound Level Category:	Medium	Medium	Medium	Medium	
Mode of Operation:	Continuous	Slow Pulse @ 1 PPS	Fast Pulse @ 10 PPS	Chime @ Once per 3 Seconds	
Loudness @ 2 FT:	75 to 85 dB(A) Typ.	75 to 85 dB(A) Typ.	75 to 85 dB(A) Typ.	75 to 85 dB(A) Typ.	
Frequency:	3900 ± 500 Hz	3900 ± 500 Hz	3900 ± 500 Hz	3700 ± 500 Hz	
Connection:	"+" to Positive, "-" to Ground	"+" to Positive, "-" and "1" to Ground	"+" to Positive, "-" and "2" to Ground	"+" to Positive, "-", "1" and "2" to Ground	
Voltage Rating:	6 to 16 VDC				
Current Draw:	40mA MAX				
Housing Material:	6/6 Nylon, Color: Black				
Storage Temperature:	-40° to +80° C				
Operating Temperature	-30° to +65° C				
Panel Mounting:	Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole.				
Knurled Nut:	Used to attach part to panel. The max recommended torque is 10 in-lbs.				
Weight (Typical):	28 g				
NEMA 3R,4X, & 12:	Approved with use of included gasket.				
cUL Recognition	cUL Recognized				
Options:	Please contact factory.				
Dimensions: Inches (mm)		cUL Recognized		ROHS Compliant	
		PATENT NUMBER		9576442	
					