



Mating face according to MIL-C-24308 / DIN 41 652 / CECC 75301-802


No. 1 contact



Printed board layout (1,6±0,2 thick)
View component side
(PCB plating = Tin)



No. 1 contact



							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub male standard 25 poles with solder pins and screw-lock	Maßstab/ Scale 1,5:1
						Detail.	23-NOV-01	JB			
						Insp.					
						Stand.					
09 66 323 6803	4-40 UNC	2									
09 66 323 7803	4-40 UNC	3									
09 66 323 5803	4-40 UNC	0,76 µm Au	29733	23-NOV-01	JB	HARTING EURL F-95972 Paris				TB 09 66 323 X80X	Blatt/ Page 3
Part number	screw-lock	Performance level	Mod.	Dat.	Name						