


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.






PART#	COLOR	DESCRIPTION	WEIGHT*
CJS688TGY	BLACK	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. WIRE CAP LABEL IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)
CJS688TRD	RED		
CJS688TGB	BLUE		
CJS688TGG	GREEN		
CJS688TGV	VIOLET		
CJS688TGW	WHITE		
CJS688TGYL	YELLOW		

*WEIGHT IS APPROXIMATE

NOTES :

1. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
2. MATERIAL:
MODULE HOUSING-ABS
SHIELD-TIN PLATED OVER PHOS. BRONZE
WIRE CAP/CLIP - ZINC AND PC
3. ALL TX6 PLUS, 8 POSITION, 8 WIRE JACK
MODULES ARE UNIVERSAL IN DESIGN.
THEY ACCEPT SIX AND EIGHT POSITION
MODULAR PLUGS WITHOUT DAMAGE.
4. DIMENSIONS IN PARENTHESES ARE IN
METRIC.
5. .187 x .010" GROUNDING TAB PROVIDED AS
OPTIONAL CONDUCTIVE PATH FOR GROUNDING.



PART NUMBER		CJS688TG**Y	
TITLE			
TX6 PLUS SHIELDED JACK MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479NS/08	
DATASET FILE NAME		M02479NS_DC357/08B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03 [.8]		MATERIAL: SEE NOTE 2	
 THIRD ANGLE PROJECTION		DRAWING NUMBER: 02479-357	
DRAWN BY	DATE	CHK	SCALE
AFW	3-11-06	CEF	FULL
SHT 1 OF 1			SIZE
			A

6	4-12-18	BJN	MDJR	TMBA	ADDED WHITE TO COLOR OPTIONS	02479-357
5	2-16-17	ROJC	NAGL	TMBA	MODEL REVISION UPDATED REMOVED PREVIOUS REVISIONS FOR CLARITY.	02479-357
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN