


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	A	RELEASED	19JUN2007	RD	RL	
	B	ECR-08-025212	07OCT2008	JvdH	RL	




- NOTES:
- MATERIAL CONTACTS: COPPER
 - PLATING CONTACTS: SILVER 5µm MIN OVER 1,2µm NICKEL MIN.
 - MATERIAL HOUSING: PA 4.6/30% GF Natural
 - PLATING BOARD LOCKS: 5µm Sn MIN OVER 2,5µm Ni MIN.




SCALE 15:2



RECOMMENDED PCB LAYOUT FOR 1,6mm THK PC BOARD
SCALE 2:1



SECTION A-A
SCALE 5:1



ORDERNUMBER: 1982101-1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN R. Daamen	19JUN07	tyco Electronics		Tyco Electronics Nederland BV 's-Hertogenbosch, The Netherlands	
DIMENSIONS: mm		CHK R. Lokker	-	NAME SOCKET HEADER RA, 2 POS UNIVERSAL MATE-N-LOK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J Broeksteeg	-	PRODUCT SPEC -			
		APPLICATION SPEC -		SIZE A2	CAGE CODE 00779	DRAWING NO C-1982101	RESTRICTED TO -
MATERIAL -		WEIGHT -		SCALE 5:1		SHEET 1	OF 1
-		CUSTOMER DRAWING		REV B			