

Search within category

GO

PPMA1125A

COMPRESSED AIR

Self-Stick Pipe Marker, 'COMPRESSED AIR' (legend), Yellow, Size A.
Sold in US and Canada only

BUY NOW

DESIGN / INSTALL

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Material	Dura-Polyester Vinyl			
Overall Width (mm)	203.2			
Overall Height (mm)	25.4			
Note	Sold in US and Canada only			
Application	Mark and identify contents in pipes and piping systems, including flow directions and hazard classification for maintenance and safety purposes. Pipe markers are designed in accordance to ASME (ANSI) A13.1 recommendations for sizes, colors, and visibility.			
Color	Black/Yellow			
Diameter (mm)	31.75			
Dimensions (In.)	1" x 8"			
Environment	5-7 years			
Legend	COMPRESSED AIR			
Maximum Operating Temperature (°C)	80			
Maximum Operating Temperature (°F)	176			
Maximum Overall Height (mm)	25.4			
Minimum Operating Temperature (°C)	-28			
Minimum Operating Temperature (°F)	-20			
Part Features	6-mil thick poly-composite vinyl with permanent acrylic adhesive backing scored liner for quick peel-off to apply onto pipe., Sub-surface image is protected by a high-gloss UV protective coating and is resistant to abrasions, humidity, chemicals, solvents, and fading from sunlight, Includes detachable arrow to provide proper directional flow marking, Fits pipe diameter .75" to 1.25"			
Thickness (mm)	0.1016			
UL Listed	No			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			
Sub Brand	Stock Pipe Markers			