1377174-4 Product Details



Active

Ring and Spade Tongue Terminals

SMP 0-0130496-0

1377174-4

TE Internal Number: 1377174-4

Product Highlights View All

- Terminal Shape = Spade Tongue
- Receptacle Style = Straight
- Body Style = PIDG
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

Pricing & Availability
Request Sample
Add to My Part List
Buy Product through Distributor

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Insulation	Yes
Insulation Support	Insulation Support
Stud Size	8 [M4]
Shape	SPADE-020
Heavy Duty	No
Finish	Tin
Color	Yellow

Electrical Characteristics

Voltage (VAC)	300

Termination Features

Wire/Cable Size (CMA)	5,180 – 13,100

Dimensions

Insulation Diameter (mm [in])	6.40 [.251] Max.
Stud Diameter (mm [in])	4.70 [0.185]
Tongue Material Thickness (mm [in])	1.07 [0.042]

Body Features

Body Style	PIDG
Wire Range (mm [AWG])	3.00-6.00² [12-10]
Material	Copper

Contact Features

Terminal Shape	Spade Tongue

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Range (°C)	105

Packaging Features

Packaging Method	Small Pack
Packaging Quantity	50

Other

Brand	AMP
Comment	Shipper qty= 20 X qty/plastic box for all part numbers. Bulk number 0-0130496-0

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

Provide Website Feedback

Feedback

Downloaded from Arrow.com.