



V-Bit Cutter - 0.5" Diameter, 60 Degree, #302 (2 Pack)

TOL-14859

DESCRIPTION

INCLUDES

FEATURES

- Cutting Diameter: 0.5"
- Cutting Length: 0.25"
- Shank Diameter: 0.25"
- 60° Cutting Angle
- 2 Flute

Tags

CARBIDE 3D

CNC

CUTTER

FABRICATION

MILLING

NOMAD

SHAPEOKO

TOOLS

V-BIT

© images are CC BY 2.0



COMMENTS

0

REVIEWS

0

Comments

⚙ Looking for answers to technical questions?

We welcome your comments and suggestions below. However, if you are looking for solutions to technical questions please see our [Technical Assistance](#) page.

[Log in](#) or [register](#) to post comments.



STAY IN TOUCH WITH US

Email address

SUBMIT

Weekly product releases, special offers, and more.





ABOUT SPARKFUN

[Read Our Story](#)
[Press & Media](#)
[SparkFun Education](#) 
[Job Openings](#)

PARTNER WITH US

[See Our Partners](#)
[Become a Distributor/Reseller](#)
[Receive Volume Discounts](#)
[Build a Custom Kit](#)
[Apply for a Hardware Donation](#)

SUPPORT

[Customer Support](#)
[Purchase Orders & Payment](#)
[Terms](#)
[Technical Assistance](#)
[FAQs](#)
[Contact Us](#)

SITE INFORMATION

[Terms of Service](#)
[Privacy Policy](#)
[Compliance](#)
[Site Map](#)

SparkFun Electronics® / **6333 Dry Creek Parkway, Niwot, Colorado 80503**

Questions? Feedback? powered by [Olark live chat software](#)