



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Number of Positions: 26

Cable Assembly Length: .1 m [.33 ft]

Cable Color: Red

Shielded: No

Wire Size: 30 AWG

Features

Housing Features

Housing Material	LCP
------------------	-----

Electrical Characteristics

Impedance	125 Ω
-----------	-------

Contact Features

Contact Mating Area Plating Material	Gold (Au)
--------------------------------------	-----------

Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	.1 m [.33 ft]
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Configuration Features

Number of Positions	26
---------------------	----

Body Features

Cable Color	Red
-------------	-----



Cable Flammability Rating	VW-1
---------------------------	------

Operation/Application

Shielded	No
----------	----

Dimensions

Wire Size	.05 mm²
-----------	---------

Product Type Features

Cable Style	Ribbon Cable
Cable Assembly (End A)	Socket Housing
Cable Assembly (End B)	Socket Housing

Mechanical Attachment

Mating Alignment	With
------------------	------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 234207-E
SMCQ 26 M AB VV 8-23 CL * H007 137 E005



TE Part # 244837-E
SMCQ 26 M AB VV 8-13 CL * H007 137 E005



TE Part # 244855-E
SMCQ 26 M AB VV 8-03 CL * H007 137 E005




TE Part # 154764-E
SMCB 26 M AB VV 7-03 CL * 0007 137 E004

Also in the Series | ERNI SMC




Board-In Connectors(6)



Board-to-Board Headers & Receptacles(81)




Connector Adapters & Connector Savers(45)




PCB Headers & Receptacles(81)



Pluggable I/O Cable Assemblies(27)



Wire-to-Board Connector Assemblies & Housings(5)



Wire-to-Board Headers & Receptacles (3)


Customers Also Bought




TE Part #364240-E
SRCBUG A 2,54 2 6 CSI 112 E1 ADV J 2 324



TE Part #173799-E
IDCCS SMC 1,27 12 * AU AUI 100 PVC



TE Part #284697-E
SRCP 1,27 4 M 1 SMD 137 E1 094 * GU-H *



TE Part #364213-E
SRCBUG A 2,54 2 3 CSI 163 E1 ADV J 2 324



TE Part #173800-E
IDCCS SMC 1,27 12 * AU AUI 200 PVC




TE Part #364228-E
SRCBUG A 2,54 2 5 CSI 164 E1 ADV J 2 324



TE Part #364226-E
SRCBUG A 2,54 2 5 CSI 112 E1 ADV J 2 324



TE Part #838464-E
IDCCS SMC 1,27 50 * AU AUI 45 HF 2 324



Documents

CAD Files

Customer View Model

ENG_CVM_CVM_173796-E_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_173796-E_C.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_173796-E_C.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet - ERNI SMC 1.27mm Connectors

German

Datasheet - ERNI SMC 1.27mm Connectors

Datasheet - ERNI SMC 1.27mm Connectors

English

FLAT RIBBON CABLE ASSEMBLY (IDCCS) - SMC CONNECTOR TYPE

English