


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



- NOTE:
- MATERIAL, HOUSING: HIGH TEMP THERMAL PLASTIC, UL94-V0
TERMINAL: COPPER ALLOY
 - FINISH: TERMINAL: GOLD AT CONTACT, G/F OVER $1\mu\text{M}(40\text{u"})$ MIN NI OVER ALL
 - SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1517
 - THE HSG. WILL WITHSTAND EXPOSURE TO 260C PEAK TEMP. FOR 10 SEC. IN A WAVE SOLDER APPLICATION.
 - MATING SIDE LENGTH: 2.5MM MIN.
 - PRODUCT NUMBERING:
200218 1 1 - XXX XX X X LF

LEAD FREE
 PLATING:
 1: G/F ALL OVER
 4: 0.25UM(10U") GOLD AT CONTACT
 8: 0.76UM(30U") GOLD AT CONTACT
 PACKING
 T: TUBE
 PIN COUNT
 04, 06, 08, ..., 98, A0
 (EVERY EVEN PIN)
 STACK HEIGHT "K"
 EXAMPLE: 045=4.5MM
 IN 0.5MM INCREMENT



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.38		projection	title 1.27X1.27MM BTB STACK HD VT, TH		
A	T10-0065	S.LIN	10'-5-20		.XX ± 0.25					
					.XXX ± 0.15					
				angles	0' $\pm 2'$		MM	product family 585		code
				dr	STERLING LIN	10'-5-20		size		TWN
				engr	STERLING LIN	10'-5-20		dwg no		sheet
				chr	STERLING LIN	10'-5-20	scale	A4		1 of
				appd	GARY HSIEH	10'-5-20		NA		
sheet index	revision sheet	A	1							