

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Connector
- ? Connector Type = Standard
- ? 2.54 mm Centerline
- ? Row-to -Row Spacing = 5.08 mm
- ? 40 Dual Positions

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

CAD Files:
? None Available

Product Line Information

? Tooling

- ? Product Type = Connector
- ? Connector Type = Standard
- ? Number of Dual Positions = 40
- ? Mounting Ears = With
- ? Mounting Ear Position = Flush
- ? Mounting Ear Style = With 3.18 [.125] Thru Hole
- ? PCB Retention Feature = No
- ? PCB Mount Angle = Vertical
- ? Post Type = Solder

? Termination (Solder) Post Length (mm [in]) = 5.59 [0.220]

? Solder Tail Contact Plating = Matte Tin

? Centerline (mm [in]) = 2.54 [0.100]
 ? Row-to -Row Spacing (mm [in]) = 5.08 [0.200]
 ? Card Slot Depth (mm [in]) = 7.62 [0.300]

? Contact Material = High Strength Copper Alloy

? Contact Mating Area Plating Material = Gold (30) over Nickel

?	Housing Material = Thermoplastic Glass Reinforced	
?	Housing Color = Black	
?	Housing Flammability Rating = UL 94V	-0

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Brand = Tyco Electronics