



Search by part # or keyword



Products

Industries &
Solutions

Resources

TE Store

Sign In

[Connectors](#) > [Power Connectors, Contacts, & Terminals](#) > [Circular Power](#) > [Circular Power Co](#)**Purchase items directly
from TE.com**

5-862549-4

LGH 1 SNGL MLD END POS. STOP



LGH

TE Internal #: **5-862549-4**TE Internal Description: **LGH 1 SNGL MLD
END POS. STOP**Product Type : **Lead Assembly**Operating Voltage (VDC): **20000**Wire Size (AWG): **16**Operating Temperature Range (°C): **-55 – 125**Shielded : **No**[Similar Products](#) | [Download Digital Datasheet](#)**Compatible Parts & Tooling****Free Shipping** to select countries.Exclusions apply. See complete details
at [TE Store FAQs](#)

QTY:

Extended Price:

We are here to help!

Get in touch with our product experts.

**CHAT WITH US****EMAIL US****CALL US****Documents****Features****Product Compliance**

Product Drawings

[LEAD ASSEMBLY, POS STOP SGL END, LGH-1](#) .tif

English

[LGH 1 SNGL MLD END POS. STOP](#)[Download LGH 1 SNGL MLD END POS. STOP](#) English

CAD Files

3D PDF

[Download 3D_CVM_CVM_5-862549-4_W.pdf](#) 3D

Customer View Model

[Download ENG_CVM_CVM_5-862549-4_W.2d_dxf.zip](#)

English

[Download ENG_CVM_CVM_5-862549-4_W.3d_igs.zip](#)

English

[Download ENG_CVM_CVM_5-862549-4_W.3d_stp.zip](#)

English

Datasheets &
Catalog Pages

Products for Aerospace and Defense

[ENG_DS_1308940_Aerospace_Defense_0118.pdf](#)

English

Product
Specifications

Product Specification

[Download ENG_SS_108-36033_O2.pdf](#) English

Product Environmental Compliance	REACH Substance Communication Document ENG_PC_RSCD_Lead_1.pdf English
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.	
Product Type Features	Product Type : Lead Assembly
Electrical Characteristics	Operating Voltage (VDC): 20000
Dimensions	Wire Size (AWG): 16 Assembly Length : 304.8 mm [12 in] Pigtail Length : 9.65 mm [.38 in]
Usage Conditions	Operating Temperature Range (°C): -55 – 125 Shielded : No
Statement of Compliance	Statement of Compliance pdf

Products with Similar Specs

View All Similar Products

THIS PRODUCT	TOP RESULTS ?		
CIRCULAR POWER CONNECTORS 5-862549-4 LGH 1 SNGL MLD END POS. STOP  From In-Stock Product Type : Lead Assembly Operating Voltage : 20000 VDC Wire Size : 16 AWG Operating Temperature Range : -55 – 125 °C Shielded : No	CIRCULAR POWER CONNECTORS 5-862545-4 LEAD, SGL END ASSY, LGH  Non-Stocked Product Type : Lead Assembly Operating Voltage : 10000 VDC Wire Size : 16 AWG Operating Temperature Range : -55 – 125 °C Shielded : No	CIRCULAR POWER CONNECTORS 5-862547-4 LEAD, SGL END ASSY, LGH  Non-Stocked Product Type : Lead Assembly Operating Voltage : 15000 VDC Wire Size : 16 AWG Operating Temperature Range : -55 – 125 °C Shielded : No	CIRCULAR POWER CONNECTORS 5-862551-4 LGH-1L SGL MOLDED END LEAD  Non-Stocked Product Type : Lead Assembly Operating Voltage : 25000 VDC Wire Size : 16 AWG Operating Temperature Range : -55 – 125 °C Shielded : No

