Your Expert Partner for **Human Machine Interfaces**

Actuator

61-
3440.4/8



https://www.eao.com/component/61-3440.4/8/en/...

Downloaded from Arrow.com.

Your product:



61-3440.4/8
Actuator

MOUNTING

Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	Grey
Lens material:	Plastic
Lens illumination:	Non illuminated
Lens shape:	Mushroom-head
Lens optics:	opaque

MECHANICAL CHARACTERISTICS

Switching action:	Maintained
Release type:	Twist to unlock
Tightening torque:	Max. 0.5 Nm
Weight:	0.02 kg

AMBIENT CONDITION

Operating temperature:	– 25 °C ... + 55 °C

CERTIFICATE

REACH:	REACH compliant
RoHS:	RoHS compliant

Downloaded from Arrow.com.

OTHER

Short Description: Actuator, Mushroom-head, Non illuminated, Grey, Plastic, opaque, Maintained, Twist to unlock


Housing colour: Grey

Housing material: Plastic


Marking: Arrows

Product attributes: Twist to unlock clockwise


Wiring diagrams:



Mounting cut-outs:



Dimension drawings:



A = Plug-in terminal 2.8 mm x 0.5 mm
C = Screw terminal

Downloaded from Arrow.com.