

OGA DIAGONAL: 16.40 [416.59]
VA DIAGONAL: 15.68 [398.29]
PA DIAGONAL: 14.79 [375.72]

ESD CLAMHELL
CASE
IS USED WITH ALL
NOV, USB AND SER
TERMINATIONS.

(NOV)

PIN #1

(SER)

EXII-7720SC
98-0003-2217-6
SERIAL CONTROLLER
SOLDER SIDE

PIN #1

(HID M)

EXII-7730HC
98-0003-2813-2
HID CONTROLLER
SOLDER SIDE

(USB R)


EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE

PIN #1

(FFC)

PIN #1
SEE NOTE 2

.147±.020 [3.73±.51]
TOTAL THICKNESS
OF GLASS, CABLE
AND STRAIN RELIEF



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 639 ±10%
2. 5 PIN AMP CONNECTOR
LATCH STYLE HOUSING P/N: 487526-4
TIN CONTACTS P/N: 2-487406-4
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHLD
4	UL
5	UR

TOP LEVEL NUMBER	SKU 98 NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8031-203	98-0003-2511-2	FFC	4.27" [108.46]	AG500	23655
17-8031-204	98-0003-2513-8	FFC	6.00" [152.40]	AG500	23655
17-8031-205	98-0003-2514-6	FFC	8.00" [203.20]	AG500	23655
17-8031-206	98-0003-2515-3	NOV	SEE DWG	AG500	23655
17-8031-221	98-0003-2521-1	SER	4.27" [108.46]	AG500	23655
17-8031-223	98-0003-2522-9	SER	6.00" [152.40]	AG500	23655
17-8031-227	98-0003-2525-2	SER	8.00" [203.20]	AG500	23655
17-8031-218	98-0003-2519-5	USB R	4.27" [108.46]	AG500	23655
17-8031-226	98-0003-2919-7	USB R	8.00" [203.20]	AG500	23655
17-8031-230	98-0003-2921-3	HID M	8.00" [203.20]	AG500	23655

PINOUT	
1	LR
2	LL
3	SHLD
4	UL
5	UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	±
.XX	±.03 [.76]
.XXX	±.015 [.38]
ANGLES	±1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE	1 = 1

	3M TOUCH SYSTEMS METHUEN, MA USA
© COPYRIGHT 2005 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.	
DRAWN	K. CROWLEY 9/05

05	REVISED PER CO 030743	7/09	SB
04	REVISED PER CO 028873	5/08	SEB
03	REVISED PER CO 028687	2/08	ACM
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING SCT32NN 15.68"			
CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE	DOCUMENT NO.	REV	
C	28138-MKT		05