

48-Port 1U Rack-Mount Cat6/Cat5 High Density 110 Patch Panel, 568B, RJ45 Ethernet, TAA

MODEL NUMBER: N252-048-1U



Highlights

- Space saving CAT6 Rated 48-port 1U 110 type Patch panel
- Removable "upper-deck" for easy punch down termination
- Built-in wire management loom
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 48port, 1U, Cat6 110 punch down patch panel

Description

This 1U 48-port Cat6 high-density patch panel frees up valuable rack real estate by condensing a typical 2U 48-port patch panel into 1U of space. The unique design allows for easy punch-down termination. Simply unscrew four slotted thumbscrews to remove the "upper deck" punch-down array. Punch down the "lower-deck" cables first, then replace the upper deck, and punch down upper array. Integrated wire loom keeps cabling tidy and easy to route. Heavy-duty 14GA cold-rolled steel construction. 110 connectors are color-coded for either 568A or 568B wiring. UTP Cat6 22-24 AWG solid cable

Features

- Space saving CAT6 Rated 48-port 1U 110 type Patch panel
- Removable "upper-deck" for easy punch down termination
- Built-in wire management loom
- Color coded for 568A/568B wiring
- Heavy Duty 14ga cold rolled steel construction
- Mounts in standard 19" Racks or Cabinets

Specifications

OVERVIEW	
UPC Code	037332151735
Product Type	Rackmount
Technology	Cat5/5e; Cat6
CONNECTIONS	
Number of Ports	48
Side A - Connector 1	110 IDC



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	RJ45 (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.00 x 19.50 x 3.70
Shipping Dimensions (hwd / cm)	5.08 x 49.53 x 9.40
Shipping Weight (lbs.)	3.96
Shipping Weight (kg)	1.80
Unit Dimensions (hwd / in.)	1.720 x 19.000 x 3.310
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 10.16
Unit Weight (lbs.)	3.60
Unit Weight (kg)	1.63
Panel Style	Punchdown
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.