



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APPD
A	INITIAL RELEASE	JUL06/20	S.M.




NOTES:

- MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU & AMENDMENTS.
 - HOUSING: ENGINEERING THERMOPLASTIC, UL FLAMMABILITY RATING 94V-0, COLOUR BLACK
 - POWER CONTACT: COPPER ALLOY, PLATED WITH TIN OVER NICKEL
 - DIMMABLE CONTACT: COPPER ALLOY, PLATED WITH 0.76µm (30µ") GOLD OVER 1.27µm (50µ") NICKEL.
 - GASKET: EPDM RUBBER
 - O-RING: SILICONE RUBBER
- ELECTRICAL CHARACTERISTICS:
 - HIGH VOLTAGE CURRENT: 15A
 - DIMMABLE CONTROL: 0 - 10V
 - OPERATING VOLTAGE: 480V
- SPECIFICATIONS:
 - ANSI C136-41-2017
 - ANSI C136-10-2010
 - UL 773



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.




ORDERING CODE: **FLB - P8X 001**

FLB SERIES ANSI C136-41
 X = NUMBER OF CONTACTS
 0 = 3 POWER CONTACTS ONLY
 5 = 3 POWER AND 2 SIGNAL CONTACTS
 7 = 3 POWER AND 4 SIGNAL CONTACTS


001 - STANDARD
 002 - VENTED BASE

MATING COVERS CAN ORDERED SEPARATELY PART NO. FLB-C80-XXX-001
 AMPHENOL PART NUMBER FLB-P8X-001


UNLESS SPECIFIED OTHERWISE		DRAWN	S.MUGAN	JUL06/20	Amphenol Canada Corp. Commercial Products FLB SERIES, DIMMING CONTROL, LOCKING TYPE BASE, RoHS COMPLIANT				
PRIMARY UNITS	MILLIMETERS	CHECKED	A.GREEN	JUL06/20					
SECONDARY	INCHES	M.E. APP'D							
REFERENCE IN PARENTHESES		Q.A. APP'D							
GENERAL TOLERANCES		DWG APPR.							
1 DECIMAL PLACE	±0.3	ENG. REL. NO.			DWG. NO. P-FLB-P8X-001				
2 DECIMAL PLACES		REF.							
3 DECIMAL PLACES		THIRD ANGLE PROJECTION  DO NOT SCALE DRAWING							
ANGULAR DEGREES					CODE ID NO. 03554 DWG SIZE: X SCALE: 2:1 SHEET 1 OF 2				




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APPD
D	UPDATED PRODUCT RELEASE	MAY12/20	S.M.
E	UPDATED PART NUMBER	JUN5/20	S.M.



FLB-P70-001 SHOWN
NO DIMMING CONTACTS



FLB-C70-XXX-001
PCB



FLB-P75-001
2 DIMMING CONTACTS



UNLESS SPECIFIED OTHERWISE		DRAWN	S.MUGAN	APR01/08
PRIMARY UNITS	MILLIMETRES	CHECKED	A.GREEN	APR01/08
SECONDARY	INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES		Q.A. APP'D		
GENERAL TOLERANCES		DWG APPR.		
1 DECIMAL PLACE	±0.X	ENG. REL. NO.		
2 DECIMAL PLACES	±0.XX	REF.		
3 DECIMAL PLACES	±0.XXX	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	±X°	DO NOT SCALE DRAWING		

Amphenol Canada Corp. Commercial Products			
FLB SERIES, DIMMING CONTROL LOCKING TYPE BASE, RoHS COMPLIANT			
DWG. NO. P-FLB-P7X-001			REV E
CODE ID NO. 03554	DWG SIZE: X	SCALE: 2:1	SHEET 2 OF 2