






PCB Layout, component side (thickness 1.6 mm min.)

Max. Temperature : 260° during 10 seconds

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-SUB SMT Low Profile Female 9p with die casted grounds and M3 unremovable screwlocks	Maßstab/ Scale 1,5:1	
			Detail.	28Aug2009	ED				
			Insp.						
			Stand.						
EC01215	14 Jan 2010	ED	HARTING EURL F-95972 Paris					TB 09 55 156 x619	Blatt/ Page 1 / 2
EC00775	28Aug2009	ED							
Mod.	Dot.	Name							
							Sub.		



				Dat.	Name		D-SUB SMT Low Profile Female 9p with die casted grounds and M3 unremovable screwlocks	Maßstab/ Scale
			Detail.	28Aug2009	ED			
			Insp.					
EC01215	14Jan2010	ED	Stand.			All Dim. in mm Orig. Size DIN A 4	TB 09 55 156 x619	Blatt/ Page 2 / 2
EC01118	26Nov2009	LP	HARTING EURL F-95972 Paris					
EC00775	28Aug2009	ED						
Mod.	Dat.	Name						
						Sub.		