

**Part Number :** [1300390336](#)

**Product Description :** DeviceNet Mini-Change Pass-Through 4 Port

**Series Number :** 130039

**Status :** Active

**Product Category :** Passive Distribution Boxes

**Engineering Part Number :** DN2100




## Documents and Resources

### Drawings

[1300390336 sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Sodium perborate; perboric acid, sodium salt; Arsenic acid (H3AsO4), triethyl ester; Dibutylphthalate; 2,4-Dinitrotoluene; Tris(2-chloroethyl) phosphate; Tetraboron disodium heptaoxide, hydrate... per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Passive Distribution Boxes
Series	130039
Description	DeviceNet Mini-Change Pass-Through 4 Port
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	DeviceNet,Mini-Change
UPC	78678889504

### Agency

UL	E152210
----	---------

### Electrical

Current - Maximum per Contact	7.0A
Functional Wiring	Parallel
Voltage - Maximum	120V AC/DC
Wiring Configuration	Passive Pass-thru Drop

### Physical

Bus I/O	Mini-Change
Cable Connector Orientation	N/A
Cable Length	N/A

Home Run Cable Length	N/A
Home Run Connector	N/A
Home Run Interface	N/A
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	847.000/g
Orientation	Side Mount
Poles	5
Poles (wired)	4
Ports	2
Temperature Range - Operating	0° to +60°C

---

This document was generated on May 05, 2026