





Rev	AWO #	Description	Date	Appr
-		RELEASED	5/04/09	

APPROVED: _____
 DATE: _____ TITLE: _____



RECOMMENDED
PCB LAYOUT



A = .100 [2.54] X No. of Positions.
 B = .100 [2.54] X No. of Spaces.

SPECIFICATIONS:

- Material: Insulator: HI-temp thermoplastic, rated UL 94V-0
- Insulator color: Black
- Contacts: Brass
- Plating: Tin over Copper underplate overall
- Electrical: Current rating: 3 Amps max
- Contact resistance: 20 mohms max. Initial
- Insulation resistance: 5000 Mohms min @ 500 VDC
- Temperature Rating: Operating temperature: -40°C to +105°C
- Environmental: Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: DUAL ROW PIN HEADER, .100" [2.54mm]
 PITCH, TIN PLATED, 4 TO 80 PINS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLES
.X ± .10	ØXX ± .10
.XX ± .020	ØXXX ± .015
.XXX ± .015	ØXXXX ± .010
APPROVALS	DATE
DRAWN DY	5/04/09
CHECKED	
APPROVED	

SIZE	PART NO.	REV.
X	PH2-XX-TAHT	-
REF:	SCALE: NTS	SHEET 1 OF 1