





Rev	AWO #	Description	Date	Appr
-		RELEASED	10/02/12	

APPROVED: _____

DATE: _____ TITLE: _____



Panel hole dimensions



SPECIFICATIONS:

Material: Nylon66, rated UL 94V-2

Insulator color: Natural

Electrical:

Voltage Rating: 600V Max.

Current rating: 11 Amps Max.

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 5,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES	HILES	±.10	±.015	250 [6.35MM] PITCH CONNECTOR, 6 POS HOUSINGS, MALE, VERTICAL			
.X	±.10	±.015	±.010				
.XX	±.020	±.015	±.010				
.XXX	±.015	±.010	±.010				
APPROVALS				TITLE			
DATE	DATE	DATE	DATE	SIZE			
DRAWN	TW	10/02/12	10/02/12	PART NO.			
CHECKED	AV	10/02/12	10/02/12	DME-M-06-SQ			
APPROVED				REV.			
				REF: S00123T			
				SCALE: NTS			
				SHEET 1 OF 2			