

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301080151

Status:

Active

Overview:

Wide-Area Lighting Products

Description:

Super-Safeway Twin Tube 30W Fluorescent Work Light, Cord Type 16/3 SJOW 7.62m (25.0') Cord Length

Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E174254
General	
Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Wide-Area Lighting Products
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678867260
Physical	
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	190.75mm (7.510")
Duty	Industrial
Guard Included	Yes
Guard Type	Clear Butyrate
Height	82.55mm (3.250")
Length	625.35mm (24.620")
Material - Guard	Butyrate
Mounting Style	Straps
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Fluorescent
Cord Type - Primary	16/3 SJOW
Lamp Type	F15/T8
Lamp Wattage - Maximum	30W
Lumens	1820
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	1324



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
130108 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION