Part Number : 1301470117
Product Description : Watertite Extreme Connector for Male Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, Neman L21-30, 3ø 208V, F4
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 29W81MB



Documents and Resources

Drawings

1301470117_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Connector for Male Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, Neman L21-30, 3ø 208V, F4
IP Rating	IP69K
NEMA Configuration	NEMA L21-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871417

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 208V

Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	No
Flip Lid	No

Downloaded from Arrow.com.

Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	4-pole/5-wire
Receptacle Type	Single

Downloaded from Arrow.com.