


Han 3M RJ45 Hybrid Cat.6 PFT 8+4p

Spotted an error? |  [Print page](#) [Back](#)



Image is for illustration purposes only.
Please refer to product description.

- [Features](#)[Connection data](#)[Dimensions and weight](#)[Supplementals](#)

Part number:	09 45 215 1761
Description:	Han 3M RJ45 Hybrid Cat.6 PFT 8+4p
Type sheet:	 PDF

Features

Application:	1/10Gbit Ethernet + Power 48V/16A 10/100Mbit Ethernet + Power 48V/16A
Class of Protection:	IP65 / IP67
Mating face:	RJ45 + 4x Power 48V/16A
No. of contacts:	Data: 8 / Power: 4
RoHS conformity:	Yes
Termination Type:	Data: Piercing Contact / Power: IDC
Type:	RJ45 Hybrid / Cat.6

⏮ Top

Connection data

Rated Voltage:	Data: 125V AC / Power 48V DC
----------------	------------------------------

⏮ Top

Dimensions and weight

Net Weight:	79.9 g
-------------	--------

⏮ Top

Supplementals

Series:	Han@ 3A RJ45 Hybrid (Variant 5)
---------	---------------------------------

⏮ Top

[Login to MyHARTING](#)
for pricing and stock check

Quantity: 1

[Shopping cart](#)

[Email inquiry](#)

Need assistance?



Customer service

Your HARTING customer
service representative:

866-278-0306

[CustomerService-USA@HA ...](#)

Catalogue

HARTING Device Connectivity -
Page 304



 [Browse](#)

 [Download](#)

Downloads

Title	Download
Type sheet	 PDF
Type sheet	 DXF
Type sheet	 CGM
Assembly Instruction	 PDF
HARTING Device Connectivity - Page 304	 PDF

Recently viewed - [Delete](#)



**Han 3M RJ45 Hybrid
Cat.6 PFT 8+4p**

[Show product details](#)

Recently searched

No searches have been done yet.

