

Protect It! 3-Outlet Travel-Size Surge Protector, 18-in. (45.72 cm) Cord, 1050 Joules, 2-USB Charging Ports

MODEL NUMBER: TRAVELER3USB



Highlights

- 3 AC power outlets
- 1050 Joule rating
- Concealable 18-inch Power Cord
- 2 USB Charging Ports - 2.1 amp total (5 VDC) for fast charging of cell phones, MP3 players, smartphones, tablets and more

Package Includes

- TRAVELER3USB Surge Suppressor
- Users Manual

Features

- 1050 joules of AC surge suppression shields equipment from the strongest surges and line noise
- 3 AC outlets with room for 1 transformer plug without blocking outlets
- 2 USB Charging Ports with 2.1 amps total is great for fast charging of cell phones, MP3 player, tablets, laptops and more.
- Portable housing with 18-in. concealable cord allow for ease of mobility and travel in briefcases
- "Protected" Diagnostic LED confirms outlet surge suppression status
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332149626
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)

Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT 3/C
Input Cord Length (ft.)	1.5
Right-Angle Plug	Yes
Input Cord Length (m)	0.46
Integrated Cord Clip	No
OUTPUT	
Output Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output Receptacles	(3) 5-15R
Transformer Accommodation	(2) Yes
Output Amp Capacity	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirm suppressor "protection present" (green) status
CHARGING	
Number of Charging Ports	2
Total Charging Watts	10.5
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.1A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No

Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	7.70 x 2.50 x 3.40
Shipping Dimensions (hwd / cm)	19.56 x 6.35 x 8.64
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
Unit Dimensions (hwd / in.)	5.700 x 2.960 x 1.400
Unit Dimensions (hwd / cm)	14.48 x 7.52 x 3.56
Unit Weight (lbs.)	.62
Unit Weight (kg)	0.28
CONNECTIONS	
Number of Ports	2
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.